

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206870

Luminaire Tested: **LD4B40D010 EU4B30508035 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206870
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508035 4LBWGPH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2741.4 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206870

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P206870

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92				92
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76				76
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63				63
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57				57
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53				53
8	73	62	56	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48				48
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45				45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41				41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206870

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.1	6.8
10°-20°	527.4	19.2
20°-30°	756.4	27.6
30°-40°	712.2	26.0
40°-50°	393.3	14.3
50°-60°	126.2	4.6
60°-70°	31.5	1.2
70°-80°	7.5	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1469.9	53.6
0°-40°	2182.1	79.6
0°-60°	2701.6	98.6
0°-90°	2741.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2741.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1973	
5°	1964	186
15°	1868	527
25°	1659	756
35°	1155	712
45°	499	393
55°	128	126
65°	28	32
75°	5	8
85°	0	1
90°	0	



TEST NUMBER: P206870

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1973.1
2.5°	1958.8
5°	1963.5
7.5°	1949.3
10°	1925.5
12.5°	1901.7
15°	1868.5
17.5°	1839.9
20°	1792.4
22.5°	1725.8
25°	1659.3
27.5°	1568.9
30°	1450.1
32.5°	1317.0
35°	1155.3
37.5°	984.2
40°	808.2
42.5°	646.6
45°	499.2
47.5°	375.6
50°	271.0
52.5°	190.2
55°	128.4
57.5°	85.6
60°	61.8
62.5°	42.8
65°	28.5
67.5°	19.0
70°	14.3
72.5°	9.5
75°	4.8
77.5°	4.8
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)