

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208211

Luminaire Tested: **LD4B40D010 EU4B30509035 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208211
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509035 4LBMLI1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3321.3 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208211

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208211

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																												
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88																												
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83																												
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78																												
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73																												
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69																												
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65																												
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62																												
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58																												
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208211

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	474.1	14.3
10°-20°	1059.9	31.9
20°-30°	1053.7	31.7
30°-40°	573.8	17.3
40°-50°	132.6	4.0
50°-60°	18.7	0.6
60°-70°	6.9	0.2
70°-80°	1.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2587.7	77.9
0°-40°	3161.5	95.2
0°-60°	3312.8	99.7
0°-90°	3321.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3321.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5236	
5°	5128	474
15°	3826	1060
25°	2311	1054
35°	888	574
45°	153	133
55°	20	19
65°	8	7
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P208211

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBMLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5236.0
2.5°	5223.9
5°	5127.5
7.5°	4930.6
10°	4657.3
12.5°	4255.5
15°	3825.5
17.5°	3399.6
20°	2981.7
22.5°	2640.1
25°	2310.6
27.5°	1997.1
30°	1643.5
32.5°	1249.7
35°	888.1
37.5°	598.7
40°	389.8
42.5°	245.1
45°	152.7
47.5°	88.4
50°	44.2
52.5°	24.1
55°	20.1
57.5°	12.1
60°	12.1
62.5°	8.0
65°	8.0
67.5°	4.0
70°	4.0
72.5°	4.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)