

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207058

Luminaire Tested: **LD4B20D010 EU4B10209050 4LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207058  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B20D010 EU4B10209050 4LBWMW1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1541.3 lumens  
Efficiency: N/A  
Efficacy: 74.1 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207058

CATALOG NUMBER: LD4B20D010 EU4B10209050 4LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P207058

CATALOG NUMBER: LD4B20D010 EU4B10209050 4LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |   |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |   |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99  | 101 | 98  | 96  | 97  | 95  | 93  | 93  | 92  | 90  | 88  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 103 | 96  | 91  | 86  | 101 | 94  | 89  | 85  | 91  | 87  | 83  | 88  | 84  | 81  | 85  | 82  | 80  | 78  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 96  | 87  | 80  | 75  | 93  | 85  | 79  | 74  | 83  | 77  | 73  | 80  | 76  | 72  | 78  | 74  | 71  | 69  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 89  | 79  | 72  | 66  | 87  | 78  | 71  | 66  | 75  | 69  | 65  | 73  | 68  | 64  | 71  | 67  | 63  | 61  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 83  | 72  | 64  | 59  | 81  | 71  | 64  | 58  | 69  | 63  | 58  | 67  | 62  | 57  | 65  | 61  | 57  | 55  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 78  | 66  | 58  | 53  | 76  | 65  | 58  | 53  | 64  | 57  | 52  | 62  | 56  | 52  | 60  | 55  | 51  | 50  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 73  | 61  | 53  | 48  | 71  | 60  | 53  | 48  | 59  | 52  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 45  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 68  | 56  | 49  | 44  | 67  | 56  | 49  | 44  | 54  | 48  | 43  | 53  | 47  | 43  | 52  | 47  | 43  | 41  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 64  | 52  | 45  | 40  | 63  | 52  | 45  | 40  | 51  | 44  | 40  | 50  | 44  | 40  | 49  | 43  | 39  | 38  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 61  | 49  | 42  | 37  | 59  | 48  | 41  | 37  | 47  | 41  | 37  | 46  | 41  | 37  | 46  | 40  | 36  | 35  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207058

CATALOG NUMBER: LD4B20D010 EU4B10209050 4LBWMW1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 87.7   | 5.7       |
| 10°-20°   | 245.2  | 15.9      |
| 20°-30°   | 346.6  | 22.5      |
| 30°-40°   | 335.7  | 21.8      |
| 40°-50°   | 226.5  | 14.7      |
| 50°-60°   | 140.6  | 9.1       |
| 60°-70°   | 94.0   | 6.1       |
| 70°-80°   | 51.4   | 3.3       |
| 80°-90°   | 13.6   | 0.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 679.5  | 44.1      |
| 0°-40°    | 1015.2 | 65.9      |
| 0°-60°    | 1382.3 | 89.7      |
| 0°-90°    | 1541.3 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1541.3 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 934 |      |
| 5°  | 926 | 88   |
| 15° | 870 | 245  |
| 25° | 760 | 347  |
| 35° | 540 | 336  |
| 45° | 290 | 227  |
| 55° | 154 | 141  |
| 65° | 94  | 94   |
| 75° | 48  | 51   |
| 85° | 12  | 14   |
| 90° | 0   |      |



TEST NUMBER: P207058

CATALOG NUMBER: LD4B20D010 EU4B10209050 4LBMMW1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°  |
|-------|-----|
| 0°    | 934 |
| 2.5°  | 934 |
| 5°    | 926 |
| 7.5°  | 916 |
| 10°   | 904 |
| 12.5° | 892 |
| 15°   | 870 |
| 17.5° | 852 |
| 20°   | 822 |
| 22.5° | 792 |
| 25°   | 760 |
| 27.5° | 716 |
| 30°   | 668 |
| 32.5° | 606 |
| 35°   | 540 |
| 37.5° | 474 |
| 40°   | 408 |
| 42.5° | 342 |
| 45°   | 290 |
| 47.5° | 242 |
| 50°   | 206 |
| 52.5° | 176 |
| 55°   | 154 |
| 57.5° | 136 |
| 60°   | 122 |
| 62.5° | 108 |
| 65°   | 94  |
| 67.5° | 82  |
| 70°   | 70  |
| 72.5° | 60  |
| 75°   | 48  |
| 77.5° | 38  |
| 80°   | 28  |
| 82.5° | 20  |
| 85°   | 12  |
| 87.5° | 4   |
| 90°   | 0   |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)