

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205825

Luminaire Tested: **LD4B30D010 EU4B30509024 4LBSWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205825  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30509024 4LBSWH1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2082.4 lumens  
Efficiency: N/A  
Efficacy: 74.4 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205825

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBSWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205825

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBSWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205825

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBSWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.5	5.5
10°-20°	296.5	14.2
20°-30°	387.8	18.6
30°-40°	410.6	19.7
40°-50°	383.0	18.4
50°-60°	290.1	13.9
60°-70°	157.1	7.5
70°-80°	42.2	2.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	798.8	38.4
0°-40°	1209.4	58.1
0°-60°	1882.5	90.4
0°-90°	2082.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2082.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1242	
5°	1224	115
15°	1060	296
25°	843	388
35°	656	411
45°	499	383
55°	326	290
65°	157	157
75°	36	42
85°	0	1
90°	0	



TEST NUMBER: P205825

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBSWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1241.9
2.5°	1237.3
5°	1223.7
7.5°	1194.1
10°	1155.3
12.5°	1109.7
15°	1059.6
17.5°	1002.6
20°	952.5
22.5°	895.5
25°	843.1
27.5°	790.7
30°	740.6
32.5°	697.3
35°	656.3
37.5°	615.3
40°	576.5
42.5°	537.8
45°	499.0
47.5°	455.7
50°	412.4
52.5°	369.2
55°	325.9
57.5°	280.3
60°	237.0
62.5°	196.0
65°	157.2
67.5°	120.8
70°	88.9
72.5°	61.5
75°	36.5
77.5°	16.0
80°	4.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)