

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207077

Luminaire Tested: **LD4B40D010 EU4B30508040 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508040 4LBWMW1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3697.8 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207077

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207077

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88	88	88	88	88	88	88	88	88	88	88																
	2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78	78	78	78	78	78	78	78	78	78	78																
	3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69	69	69	69	69	69	69	69	69	69	69																
	4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61	61	61	61	61	61	61	61	61	61	61																
	5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55	55	55	55	55	55	55	55	55	55	55																
	6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50	50	50	50	50	50	50	50	50	50	50																
	7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45	45	45	45	45	45	45	45	45	45	45																
	8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41	41	41	41	41	41	41	41	41	41	41																
	9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38	38	38	38	38	38	38	38	38	38	38																
	10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35	35	35	35	35	35	35	35	35	35	35																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207077

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.4	5.7
10°-20°	588.3	15.9
20°-30°	831.5	22.5
30°-40°	805.4	21.8
40°-50°	543.5	14.7
50°-60°	337.3	9.1
60°-70°	225.4	6.1
70°-80°	123.3	3.3
80°-90°	32.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1630.2	44.1
0°-40°	2435.6	65.9
0°-60°	3316.4	89.7
0°-90°	3697.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3697.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2241	
5°	2222	210
15°	2087	588
25°	1823	831
35°	1296	805
45°	696	543
55°	370	337
65°	226	225
75°	115	123
85°	29	33
90°	0	



TEST NUMBER: P207077

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2240.8
2.5°	2240.8
5°	2221.6
7.5°	2197.6
10°	2168.8
12.5°	2140.0
15°	2087.2
17.5°	2044.0
20°	1972.1
22.5°	1900.1
25°	1823.3
27.5°	1717.8
30°	1602.6
32.5°	1453.9
35°	1295.5
37.5°	1137.2
40°	978.8
42.5°	820.5
45°	695.7
47.5°	580.6
50°	494.2
52.5°	422.2
55°	369.5
57.5°	326.3
60°	292.7
62.5°	259.1
65°	225.5
67.5°	196.7
70°	167.9
72.5°	143.9
75°	115.2
77.5°	91.2
80°	67.2
82.5°	48.0
85°	28.8
87.5°	9.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)