

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206443

Luminaire Tested: **LD4B30D010 EU4B30508027 4LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206443
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508027 4LBCSMB1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2727.5 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206443

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P206443

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88																
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75																
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65																
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56																
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49																
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43																
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39																
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35																
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31																
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206443

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.9	4.0
10°-20°	310.4	11.4
20°-30°	466.5	17.1
30°-40°	553.6	20.3
40°-50°	547.8	20.1
50°-60°	430.3	15.8
60°-70°	241.3	8.8
70°-80°	67.7	2.5
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	885.8	32.5
0°-40°	1439.4	52.8
0°-60°	2417.5	88.6
0°-90°	2727.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2727.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1152	
5°	1150	109
15°	1101	310
25°	1013	467
35°	888	554
45°	714	548
55°	485	430
65°	240	241
75°	59	68
85°	0	1
90°	0	



TEST NUMBER: P206443

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1151.7
2.5°	1147.8
5°	1149.8
7.5°	1140.0
10°	1128.3
12.5°	1114.6
15°	1100.9
17.5°	1083.3
20°	1059.8
22.5°	1036.4
25°	1012.9
27.5°	987.5
30°	954.2
32.5°	921.0
35°	887.7
37.5°	848.6
40°	803.7
42.5°	760.6
45°	713.7
47.5°	660.9
50°	606.2
52.5°	543.6
55°	484.9
57.5°	418.5
60°	355.9
62.5°	299.2
65°	240.5
67.5°	189.7
70°	140.8
72.5°	95.8
75°	58.7
77.5°	29.3
80°	7.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)