

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206236

Luminaire Tested: **LD4B30D010 EU4B30508027 4LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206236  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30508027 4LBPSMW1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2976.3 lumens  
Efficiency: N/A  
Efficacy: 106.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206236

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P206236

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206236

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.6	3.8
10°-20°	323.9	10.9
20°-30°	487.8	16.4
30°-40°	580.4	19.5
40°-50°	579.3	19.5
50°-60°	471.2	15.8
60°-70°	289.9	9.7
70°-80°	112.3	3.8
80°-90°	18.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	925.3	31.1
0°-40°	1505.7	50.6
0°-60°	2556.2	85.9
0°-90°	2976.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2976.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1199	
5°	1196	114
15°	1150	324
25°	1062	488
35°	929	580
45°	753	579
55°	527	471
65°	291	290
75°	102	112
85°	14	18
90°	0	



TEST NUMBER: P206236

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1199.2
2.5°	1200.9
5°	1195.6
7.5°	1188.6
10°	1179.8
12.5°	1163.9
15°	1149.8
17.5°	1128.6
20°	1105.7
22.5°	1084.5
25°	1061.6
27.5°	1029.9
30°	998.1
32.5°	968.1
35°	929.4
37.5°	887.0
40°	848.2
42.5°	800.6
45°	753.0
47.5°	701.9
50°	647.2
52.5°	590.8
55°	527.3
57.5°	465.6
60°	405.6
62.5°	347.4
65°	291.0
67.5°	238.1
70°	188.7
72.5°	142.8
75°	102.3
77.5°	67.0
80°	40.6
82.5°	24.7
85°	14.1
87.5°	7.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)