

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252095

Luminaire Tested: **LD4B30D010 EU4B30509027 4LBBA1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-4)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509027 4LBBA1MB
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE BLACK TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1198.0 lumens
Efficiency: N/A
Efficacy: 42.8 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.94
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252095

CATALOG NUMBER: LD4B30D010 EU4B30509027 4LBBA1MB

Luminous Intensity Polar Plot





TEST NUMBER: P252095

CATALOG NUMBER: LD4B30D010 EU4B30509027 4LBBA1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65		
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61		
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57		
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53		
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116765
5°	116447
10°	115320
15°	113468
20°	110143
25°	101759
30°	82556
35°	51171
40°	24083
45°	8407
50°	2365
55°	1597
60°	1228
65°	1084
70°	883
75°	602
80°	898
85°	0



TEST NUMBER: P252095

CATALOG NUMBER: LD4B30D010 EU4B30509027 4LBBA1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	9.4
10°-20°	316.1	26.4
20°-30°	424.9	35.5
30°-40°	271.5	22.7
40°-50°	57.7	4.8
50°-60°	8.7	0.7
60°-70°	4.2	0.4
70°-80°	1.9	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	853.8	71.3
0°-40°	1125.3	93.9
0°-60°	1191.7	99.5
0°-90°	1198.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1198.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1198	
5°	1190	113
15°	1125	316
25°	946	425
35°	430	271
45°	61	58
55°	9	9
65°	5	4
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P252095

CATALOG NUMBER: LD4B30D010 EU4B30509027 4LBBA1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1198.1
2.5°	1196.6
5°	1190.3
7.5°	1179.4
10°	1165.3
12.5°	1146.5
15°	1124.6
17.5°	1096.5
20°	1062.0
22.5°	1013.6
25°	946.3
27.5°	852.5
30°	733.6
32.5°	586.5
35°	430.1
37.5°	294.1
40°	189.3
42.5°	112.6
45°	61.0
47.5°	31.3
50°	15.6
52.5°	10.9
55°	9.4
57.5°	7.8
60°	6.3
62.5°	4.7
65°	4.7
67.5°	3.1
70°	3.1
72.5°	1.6
75°	1.6
77.5°	1.6
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)