

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208202

Luminaire Tested: **LD4B30D010 EU4B30509727 4LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P208202  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30509727 4LBMLI1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1954.9 lumens  
Efficiency: N/A  
Efficacy: 69.8 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P208202

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P208202

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88																			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83																			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78																			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73																			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69																			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65																			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62																			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58																			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P208202

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	279.0	14.3
10°-20°	623.8	31.9
20°-30°	620.2	31.7
30°-40°	337.7	17.3
40°-50°	78.1	4.0
50°-60°	11.0	0.6
60°-70°	4.1	0.2
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1523.1	77.9
0°-40°	1860.8	95.2
0°-60°	1949.9	99.7
0°-90°	1954.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1954.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3082	
5°	3018	279
15°	2252	624
25°	1360	620
35°	523	338
45°	90	78
55°	12	11
65°	5	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P208202

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3081.8
2.5°	3074.7
5°	3017.9
7.5°	2902.0
10°	2741.2
12.5°	2504.7
15°	2251.6
17.5°	2000.9
20°	1754.9
22.5°	1553.9
25°	1360.0
27.5°	1175.5
30°	967.3
32.5°	735.6
35°	522.7
37.5°	352.4
40°	229.4
42.5°	144.3
45°	89.9
47.5°	52.0
50°	26.0
52.5°	14.2
55°	11.8
57.5°	7.1
60°	7.1
62.5°	4.7
65°	4.7
67.5°	2.4
70°	2.4
72.5°	2.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)