

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208207

Luminaire Tested: **LD4B40D010 EU4B30508050 4LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P208207  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30508050 4LBMLI1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3969.3 lumens  
Efficiency: N/A  
Efficacy: 95.0 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P208207

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBMLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P208207

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBMLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P208207

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBMLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	566.6	14.3
10°-20°	1266.6	31.9
20°-30°	1259.3	31.7
30°-40°	685.8	17.3
40°-50°	158.5	4.0
50°-60°	22.3	0.6
60°-70°	8.3	0.2
70°-80°	1.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3092.5	77.9
0°-40°	3778.3	95.2
0°-60°	3959.1	99.7
0°-90°	3969.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3969.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6258	
5°	6128	567
15°	4572	1267
25°	2761	1259
35°	1061	686
45°	182	158
55°	24	22
65°	10	8
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P208207

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBMLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6257.5
2.5°	6243.1
5°	6127.8
7.5°	5892.5
10°	5565.9
12.5°	5085.7
15°	4571.8
17.5°	4062.8
20°	3563.3
22.5°	3155.1
25°	2761.4
27.5°	2386.8
30°	1964.2
32.5°	1493.5
35°	1061.3
37.5°	715.6
40°	465.8
42.5°	292.9
45°	182.5
47.5°	105.7
50°	52.8
52.5°	28.8
55°	24.0
57.5°	14.4
60°	14.4
62.5°	9.6
65°	9.6
67.5°	4.8
70°	4.8
72.5°	4.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)