

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206763

Luminaire Tested: **LD4B30D010 EU4B30509727 4LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206763  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30509727 4LBWWH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1808.3 lumens  
Efficiency: N/A  
Efficacy: 64.6 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206763

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P206763

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84				84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58				58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53				53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49				49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45				45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41				41

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206763

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	109.5	6.1
10°-20°	338.9	18.7
20°-30°	521.3	28.8
30°-40°	503.0	27.8
40°-50°	262.2	14.5
50°-60°	55.2	3.1
60°-70°	12.8	0.7
70°-80°	5.0	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	969.8	53.6
0°-40°	1472.7	81.4
0°-60°	1790.2	99.0
0°-90°	1808.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1808.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1131	
5°	1140	110
15°	1199	339
25°	1142	521
35°	816	503
45°	334	262
55°	50	55
65°	12	13
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P206763

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1130.6
2.5°	1133.0
5°	1140.1
7.5°	1149.6
10°	1163.8
12.5°	1182.7
15°	1199.2
17.5°	1208.7
20°	1201.6
22.5°	1187.4
25°	1142.5
27.5°	1088.1
30°	1017.1
32.5°	922.5
35°	816.1
37.5°	700.1
40°	579.5
42.5°	458.9
45°	333.5
47.5°	224.7
50°	144.3
52.5°	87.5
55°	49.7
57.5°	30.7
60°	21.3
62.5°	16.6
65°	11.8
67.5°	9.5
70°	7.1
72.5°	7.1
75°	4.7
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)