

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205837

Luminaire Tested: **LD4B40D010 EU4B30508050 4LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205837
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508050 4LBSWH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4178.7 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205837

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P205837

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89				89
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77				77
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67				67
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59				59
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35				35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205837

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.8	5.5
10°-20°	595.0	14.2
20°-30°	778.2	18.6
30°-40°	824.0	19.7
40°-50°	768.5	18.4
50°-60°	582.1	13.9
60°-70°	315.3	7.5
70°-80°	84.6	2.0
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1603.0	38.4
0°-40°	2427.0	58.1
0°-60°	3777.6	90.4
0°-90°	4178.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4178.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2492	
5°	2456	230
15°	2126	595
25°	1692	778
35°	1317	824
45°	1001	769
55°	654	582
65°	316	315
75°	73	85
85°	0	1
90°	0	



TEST NUMBER: P205837

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2492.2
2.5°	2483.0
5°	2455.6
7.5°	2396.1
10°	2318.4
12.5°	2226.9
15°	2126.3
17.5°	2012.0
20°	1911.4
22.5°	1797.1
25°	1691.9
27.5°	1586.7
30°	1486.1
32.5°	1399.3
35°	1317.0
37.5°	1234.6
40°	1156.9
42.5°	1079.2
45°	1001.4
47.5°	914.6
50°	827.7
52.5°	740.8
55°	653.9
57.5°	562.4
60°	475.6
62.5°	393.3
65°	315.5
67.5°	242.4
70°	178.3
72.5°	123.5
75°	73.2
77.5°	32.0
80°	9.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)