

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252018

Luminaire Tested: **LD4B30D010 EU4B30509030 4LBBA1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P252018  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-3)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30509030 4LBBA1MW  
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2984.0 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.99  
Luminous Opening: Circular (Dia: 0.38' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P252018

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBBA1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P252018

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBBA1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	58	50	45	68	57	50	45	56	49	45	54	49	45	53	48	44	43			
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	39	61	50	43	38	49	43	38	48	42	38	47	42	38	37			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	203385
5°	201296
10°	195251
15°	187414
20°	178987
25°	167386
30°	145699
35°	112431
40°	83191
45°	65468
50°	56235
55°	51127
60°	46604
65°	43146
70°	39864
75°	37354
80°	34685
85°	32763



TEST NUMBER: P252018

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBBA1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	193.7	6.5
10°-20°	522.0	17.5
20°-30°	706.4	23.7
30°-40°	593.5	19.9
40°-50°	375.6	12.6
50°-60°	269.8	9.0
60°-70°	185.7	6.2
70°-80°	105.1	3.5
80°-90°	32.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1422.1	47.7
0°-40°	2015.6	67.5
0°-60°	2661.0	89.2
0°-90°	2984.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2984.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2087	
5°	2058	194
15°	1858	522
25°	1557	706
35°	945	594
45°	475	376
55°	301	270
65°	187	186
75°	99	105
85°	29	32
90°	0	



TEST NUMBER: P252018

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBBA1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2086.9
2.5°	2080.3
5°	2057.6
7.5°	2020.2
10°	1973.0
12.5°	1917.7
15°	1857.5
17.5°	1792.4
20°	1725.8
22.5°	1647.7
25°	1556.6
27.5°	1439.5
30°	1294.7
32.5°	1125.6
35°	945.0
37.5°	785.6
40°	653.9
42.5°	551.4
45°	475.0
47.5°	416.4
50°	370.9
52.5°	333.4
55°	300.9
57.5°	268.4
60°	239.1
62.5°	211.5
65°	187.1
67.5°	162.7
70°	139.9
72.5°	118.7
75°	99.2
77.5°	79.7
80°	61.8
82.5°	45.5
85°	29.3
87.5°	13.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)