

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205629

Luminaire Tested: **LD4B40D010 EU4B30508050 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508050 4LBSWMH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4213.4 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205629

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P205629

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70		
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62		
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56		
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50		
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45		
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38		
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205629

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.8	5.9
10°-20°	654.1	15.5
20°-30°	878.4	20.8
30°-40°	899.2	21.3
40°-50°	778.3	18.5
50°-60°	517.7	12.3
60°-70°	212.6	5.0
70°-80°	25.3	0.6
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1779.3	42.2
0°-40°	2678.5	63.6
0°-60°	3974.4	94.3
0°-90°	4213.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4213.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2670	
5°	2629	247
15°	2336	654
25°	1916	878
35°	1436	899
45°	1014	778
55°	574	518
65°	210	213
75°	11	25
85°	0	1
90°	0	



TEST NUMBER: P205629

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2670.5
2.5°	2664.9
5°	2629.0
7.5°	2573.8
10°	2499.2
12.5°	2416.4
15°	2336.3
17.5°	2234.1
20°	2134.7
22.5°	2029.8
25°	1916.5
27.5°	1795.0
30°	1673.5
32.5°	1552.0
35°	1436.0
37.5°	1325.6
40°	1220.6
42.5°	1115.7
45°	1013.5
47.5°	905.8
50°	795.3
52.5°	684.9
55°	574.4
57.5°	477.8
60°	378.3
62.5°	287.2
65°	209.9
67.5°	138.1
70°	80.1
72.5°	38.7
75°	11.0
77.5°	5.5
80°	2.8
82.5°	2.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)