

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206975

Luminaire Tested: **LD4B40D010 EU4B30508050 4LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508050 4LBWB1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2068.7 lumens
Efficiency: N/A
Efficacy: 49.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206975

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBWB1

Luminous Intensity Polar Plot





TEST NUMBER: P206975

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	70	89	80	74	70	79	73	69	77	72	69	75	71	68	67	67	67	67
6	85	76	69	65	84	75	69	64	73	68	64	72	67	64	70	66	63	62	62	62	62
7	80	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53	53	53	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206975

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.1	7.9
10°-20°	462.0	22.3
20°-30°	638.5	30.9
30°-40°	546.7	26.4
40°-50°	232.4	11.2
50°-60°	26.0	1.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1263.6	61.1
0°-40°	1810.3	87.5
0°-60°	2068.7	100.0
0°-90°	2068.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2068.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1727	
5°	1717	163
15°	1640	462
25°	1401	638
35°	887	547
45°	293	232
55°	14	26
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P206975

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBWB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1726.8
2.5°	1722.0
5°	1717.2
7.5°	1707.6
10°	1688.4
12.5°	1678.8
15°	1640.4
17.5°	1606.9
20°	1554.1
22.5°	1491.7
25°	1400.6
27.5°	1299.9
30°	1184.8
32.5°	1045.7
35°	887.4
37.5°	724.3
40°	561.2
42.5°	417.3
45°	292.6
47.5°	182.3
50°	105.5
52.5°	52.8
55°	14.4
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)