

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206769

Luminaire Tested: **LD4B40D010 EU4B30508050 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206769
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508050 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3671.7 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206769

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206769

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92											92																	
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84											84																	
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76											76																	
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69											69																	
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63											63																	
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58											58																	
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53											53																	
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49											49																	
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45											45																	
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41											41																	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206769

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.4	6.1
10°-20°	688.1	18.7
20°-30°	1058.5	28.8
30°-40°	1021.3	27.8
40°-50°	532.5	14.5
50°-60°	112.1	3.1
60°-70°	26.0	0.7
70°-80°	10.1	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1969.0	53.6
0°-40°	2990.3	81.4
0°-60°	3634.9	99.0
0°-90°	3671.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3671.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2296	
5°	2315	222
15°	2435	688
25°	2320	1058
35°	1657	1021
45°	677	532
55°	101	112
65°	24	26
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P206769

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBWWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2295.7
2.5°	2300.5
5°	2314.9
7.5°	2334.1
10°	2363.0
12.5°	2401.4
15°	2435.0
17.5°	2454.2
20°	2439.8
22.5°	2411.0
25°	2319.7
27.5°	2209.3
30°	2065.2
32.5°	1873.1
35°	1657.0
37.5°	1421.6
40°	1176.7
42.5°	931.7
45°	677.2
47.5°	456.3
50°	293.0
52.5°	177.7
55°	100.9
57.5°	62.4
60°	43.2
62.5°	33.6
65°	24.0
67.5°	19.2
70°	14.4
72.5°	14.4
75°	9.6
77.5°	4.8
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)