

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252034

Luminaire Tested: **LD4B40D010 EU4B30509050 4LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-3)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509050 4LBBA1MW
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4264.9 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.99
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 43.02
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252034

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252034

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				46
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43				43
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39				39
10	62	50	43	39	61	50	43	38	49	43	38	48	42	38	47	42	38	37				37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	290688
5°	287709
10°	279072
15°	267869
20°	255818
25°	239240
30°	208246
35°	160699
40°	118902
45°	93557
50°	80373
55°	73080
60°	66603
65°	61664
70°	56961
75°	53395
80°	49557
85°	46741



TEST NUMBER: P252034

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.8	6.5
10°-20°	746.1	17.5
20°-30°	1009.6	23.7
30°-40°	848.3	19.9
40°-50°	536.8	12.6
50°-60°	385.6	9.0
60°-70°	265.4	6.2
70°-80°	150.2	3.5
80°-90°	46.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2032.5	47.7
0°-40°	2880.9	67.5
0°-60°	3803.2	89.2
0°-90°	4264.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4264.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2983	
5°	2941	277
15°	2655	746
25°	2225	1010
35°	1351	848
45°	679	537
55°	430	386
65°	267	265
75°	142	150
85°	42	46
90°	0	



TEST NUMBER: P252034

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBBA1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2982.7
2.5°	2973.4
5°	2940.9
7.5°	2887.4
10°	2820.0
12.5°	2740.9
15°	2654.9
17.5°	2561.9
20°	2466.6
22.5°	2355.0
25°	2224.8
27.5°	2057.4
30°	1850.5
32.5°	1608.8
35°	1350.7
37.5°	1122.9
40°	934.6
42.5°	788.1
45°	678.8
47.5°	595.1
50°	530.1
52.5°	476.6
55°	430.1
57.5°	383.6
60°	341.7
62.5°	302.2
65°	267.4
67.5°	232.5
70°	199.9
72.5°	169.7
75°	141.8
77.5°	113.9
80°	88.3
82.5°	65.1
85°	41.8
87.5°	18.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)