

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206465

Luminaire Tested: **LD4B40D010 EU4B30509050 4LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509050 4LBCSMB1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3480.7 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206465

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P206465

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88																
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75																
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65																
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56																
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49																
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43																
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39																
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35																
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31																
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206465

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.0	4.0
10°-20°	396.0	11.4
20°-30°	595.4	17.1
30°-40°	706.4	20.3
40°-50°	699.1	20.1
50°-60°	549.1	15.8
60°-70°	307.8	8.8
70°-80°	86.5	2.5
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1130.4	32.5
0°-40°	1836.8	52.8
0°-60°	3085.0	88.6
0°-90°	3480.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3480.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1470	
5°	1467	139
15°	1405	396
25°	1293	595
35°	1133	706
45°	911	699
55°	619	549
65°	307	308
75°	75	86
85°	0	1
90°	0	



TEST NUMBER: P206465

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1469.7
2.5°	1464.7
5°	1467.2
7.5°	1454.8
10°	1439.8
12.5°	1422.3
15°	1404.9
17.5°	1382.4
20°	1352.5
22.5°	1322.5
25°	1292.6
27.5°	1260.1
30°	1217.7
32.5°	1175.3
35°	1132.9
37.5°	1083.0
40°	1025.6
42.5°	970.7
45°	910.8
47.5°	843.4
50°	773.5
52.5°	693.7
55°	618.8
57.5°	534.0
60°	454.1
62.5°	381.8
65°	306.9
67.5°	242.0
70°	179.7
72.5°	122.3
75°	74.9
77.5°	37.4
80°	10.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)