

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207279

Luminaire Tested: **LD4B30D010 EU4B30509730 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207279
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509730 4LBMWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1672.8 lumens
Efficiency: N/A
Efficacy: 59.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207279

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P207279

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66			
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207279

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.5	11.0
10°-20°	471.9	28.2
20°-30°	553.6	33.1
30°-40°	350.3	20.9
40°-50°	93.8	5.6
50°-60°	13.1	0.8
60°-70°	4.9	0.3
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1209.0	72.3
0°-40°	1559.3	93.2
0°-60°	1666.3	99.6
0°-90°	1672.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1672.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1987	
5°	1954	184
15°	1690	472
25°	1223	554
35°	556	350
45°	106	94
55°	12	13
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P207279

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1986.7
2.5°	1979.3
5°	1954.5
7.5°	1915.0
10°	1858.2
12.5°	1784.0
15°	1690.1
17.5°	1593.8
20°	1477.6
22.5°	1359.0
25°	1223.1
27.5°	1074.9
30°	909.3
32.5°	728.9
35°	556.0
37.5°	402.8
40°	276.7
42.5°	177.9
45°	106.3
47.5°	59.3
50°	32.1
52.5°	17.3
55°	12.4
57.5°	9.9
60°	7.4
62.5°	7.4
65°	4.9
67.5°	2.5
70°	2.5
72.5°	2.5
75°	2.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)