

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206248

Luminaire Tested: **LD4B30D010 EU4B30509730 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509730 4LBPSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3253.3 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206248

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206248

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																												
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																												
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																												
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																												
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																												
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																												
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																												
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																												
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																												
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206248

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	3.8
10°-20°	354.0	10.9
20°-30°	533.2	16.4
30°-40°	634.4	19.5
40°-50°	633.3	19.5
50°-60°	515.0	15.8
60°-70°	316.8	9.7
70°-80°	122.7	3.8
80°-90°	19.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1011.4	31.1
0°-40°	1645.8	50.6
0°-60°	2794.1	85.9
0°-90°	3253.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3253.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1311	
5°	1307	124
15°	1257	354
25°	1160	533
35°	1016	634
45°	823	633
55°	576	515
65°	318	317
75°	112	123
85°	15	20
90°	0	



TEST NUMBER: P206248

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1310.8
2.5°	1312.7
5°	1306.9
7.5°	1299.2
10°	1289.6
12.5°	1272.2
15°	1256.8
17.5°	1233.7
20°	1208.6
22.5°	1185.5
25°	1160.4
27.5°	1125.7
30°	1091.0
32.5°	1058.3
35°	1015.9
37.5°	969.6
40°	927.2
42.5°	875.1
45°	823.1
47.5°	767.2
50°	707.4
52.5°	645.8
55°	576.4
57.5°	508.9
60°	443.4
62.5°	379.7
65°	318.1
67.5°	260.2
70°	206.3
72.5°	156.1
75°	111.8
77.5°	73.2
80°	44.3
82.5°	27.0
85°	15.4
87.5°	7.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)