

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206342

Luminaire Tested: **LD4B30D010 EU4B30508035 4LBCSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206342  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30508035 4LBCSMW1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3120.4 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206342

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P206342

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBCSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206342

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	120.7	3.9
10°-20°	343.8	11.0
20°-30°	517.1	16.6
30°-40°	612.9	19.6
40°-50°	609.9	19.5
50°-60°	491.7	15.8
60°-70°	297.4	9.5
70°-80°	110.4	3.5
80°-90°	16.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	981.7	31.5
0°-40°	1594.5	51.1
0°-60°	2696.1	86.4
0°-90°	3120.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3120.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1274	
5°	1269	121
15°	1218	344
25°	1123	517
35°	981	613
45°	794	610
55°	548	492
65°	299	297
75°	100	110
85°	13	16
90°	0	



TEST NUMBER: P206342

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1274.5
2.5°	1274.5
5°	1268.8
7.5°	1265.0
10°	1253.7
12.5°	1234.8
15°	1217.7
17.5°	1198.8
20°	1176.1
22.5°	1153.5
25°	1123.2
27.5°	1091.1
30°	1055.1
32.5°	1021.1
35°	981.4
37.5°	939.8
40°	890.6
42.5°	843.3
45°	794.2
47.5°	739.3
50°	678.8
52.5°	616.4
55°	548.4
57.5°	487.9
60°	419.8
62.5°	359.3
65°	298.8
67.5°	242.0
70°	189.1
72.5°	141.8
75°	100.2
77.5°	64.3
80°	37.8
82.5°	22.7
85°	13.2
87.5°	5.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)