

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206775

Luminaire Tested: **LD4B40D010 EU4B30509050 4LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206775  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30509050 4LBWWH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3090.9 lumens  
Efficiency: N/A  
Efficacy: 73.9 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206775

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P206775

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58	58	58	58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53	53	53	53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49	49	49	49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45	45	45	45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41	41	41	41

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206775

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.2	6.1
10°-20°	579.3	18.7
20°-30°	891.1	28.8
30°-40°	859.8	27.8
40°-50°	448.3	14.5
50°-60°	94.4	3.1
60°-70°	21.9	0.7
70°-80°	8.5	0.3
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1657.6	53.6
0°-40°	2517.3	81.4
0°-60°	3060.0	99.0
0°-90°	3090.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3090.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1933	
5°	1949	187
15°	2050	579
25°	1953	891
35°	1395	860
45°	570	448
55°	85	94
65°	20	22
75°	8	8
85°	0	1
90°	0	



TEST NUMBER: P206775

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1932.6
2.5°	1936.6
5°	1948.8
7.5°	1964.9
10°	1989.2
12.5°	2021.5
15°	2049.8
17.5°	2066.0
20°	2053.9
22.5°	2029.6
25°	1952.8
27.5°	1859.8
30°	1738.5
32.5°	1576.8
35°	1394.9
37.5°	1196.8
40°	990.6
42.5°	784.4
45°	570.1
47.5°	384.1
50°	246.6
52.5°	149.6
55°	84.9
57.5°	52.6
60°	36.4
62.5°	28.3
65°	20.2
67.5°	16.2
70°	12.1
72.5°	12.1
75°	8.1
77.5°	4.0
80°	4.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)