

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252042

Luminaire Tested: **LD4B50D010TE EU4B30509024 4LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-3)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509024 4LBBA1MW
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4498.0 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.99
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252042

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252042

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				46
8	69	58	50	45	68	57	50	45	56	49	45	54	49	45	53	48	44	43				43
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39				39
10	62	50	43	39	61	50	43	38	49	43	38	48	42	38	47	42	38	37				37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306574
5°	303421
10°	294312
15°	282509
20°	269798
25°	252316
30°	219623
35°	169479
40°	125390
45°	98670
50°	84754
55°	77073
60°	70248
65°	65031
70°	60096
75°	56332
80°	52307
85°	49313



TEST NUMBER: P252042

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	291.9	6.5
10°-20°	786.9	17.5
20°-30°	1064.8	23.7
30°-40°	894.7	19.9
40°-50°	566.2	12.6
50°-60°	406.6	9.0
60°-70°	279.9	6.2
70°-80°	158.4	3.5
80°-90°	48.7	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2143.6	47.7
0°-40°	3038.3	67.5
0°-60°	4011.0	89.2
0°-90°	4498.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4498.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3146	
5°	3102	292
15°	2800	787
25°	2346	1065
35°	1424	895
45°	716	566
55°	454	407
65°	282	280
75°	150	158
85°	44	49
90°	0	



TEST NUMBER: P252042

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBBA1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3145.7
2.5°	3135.9
5°	3101.5
7.5°	3045.1
10°	2974.0
12.5°	2890.7
15°	2800.0
17.5°	2701.9
20°	2601.4
22.5°	2483.7
25°	2346.4
27.5°	2169.8
30°	1951.6
32.5°	1696.6
35°	1424.5
37.5°	1184.2
40°	985.6
42.5°	831.2
45°	715.9
47.5°	627.7
50°	559.0
52.5°	502.6
55°	453.6
57.5°	404.5
60°	360.4
62.5°	318.7
65°	282.0
67.5°	245.2
70°	210.9
72.5°	179.0
75°	149.6
77.5°	120.1
80°	93.2
82.5°	68.7
85°	44.1
87.5°	19.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)