

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207990

Luminaire Tested: **LD4B30D010 EU4B30508035 4LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207990
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508035 4LBNMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2133.5 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207990

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207990

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 112 | 109 | 105 | 103 | 109 | 106 | 104 | 101 | 102 | 100 | 98 | 98 | 97 | 95 | 95 | 94 | 92 | 90 | | | |
| 2 | 105 | 99 | 94 | 90 | 103 | 97 | 93 | 89 | 94 | 90 | 87 | 91 | 88 | 85 | 88 | 85 | 83 | 81 | | | |
| 3 | 98 | 90 | 84 | 80 | 96 | 89 | 83 | 79 | 86 | 82 | 78 | 84 | 80 | 76 | 81 | 78 | 75 | 73 | | | |
| 4 | 92 | 83 | 76 | 71 | 90 | 82 | 76 | 71 | 80 | 74 | 70 | 78 | 73 | 69 | 76 | 72 | 68 | 67 | | | |
| 5 | 87 | 77 | 70 | 65 | 85 | 76 | 69 | 64 | 74 | 68 | 64 | 72 | 67 | 63 | 70 | 66 | 63 | 61 | | | |
| 6 | 82 | 71 | 64 | 59 | 80 | 70 | 64 | 59 | 69 | 63 | 58 | 67 | 62 | 58 | 66 | 61 | 58 | 56 | | | |
| 7 | 77 | 66 | 59 | 54 | 75 | 65 | 59 | 54 | 64 | 58 | 54 | 63 | 57 | 53 | 62 | 57 | 53 | 52 | | | |
| 8 | 73 | 62 | 55 | 50 | 71 | 61 | 55 | 50 | 60 | 54 | 50 | 59 | 53 | 49 | 58 | 53 | 49 | 48 | | | |
| 9 | 69 | 58 | 51 | 46 | 68 | 57 | 51 | 46 | 56 | 50 | 46 | 55 | 50 | 46 | 54 | 49 | 46 | 44 | | | |
| 10 | 65 | 54 | 48 | 43 | 64 | 54 | 47 | 43 | 53 | 47 | 43 | 52 | 47 | 43 | 51 | 46 | 43 | 41 | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207990

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBNMW1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 167.5 | 7.8 |
| 10°-20° | 438.1 | 20.5 |
| 20°-30° | 576.6 | 27.0 |
| 30°-40° | 448.8 | 21.0 |
| 40°-50° | 218.0 | 10.2 |
| 50°-60° | 137.7 | 6.5 |
| 60°-70° | 88.8 | 4.2 |
| 70°-80° | 46.5 | 2.2 |
| 80°-90° | 11.5 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1182.1 | 55.4 |
| 0°-40° | 1631.0 | 76.4 |
| 0°-60° | 1986.7 | 93.1 |
| 0°-90° | 2133.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2133.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1820 | |
| 5° | 1786 | 167 |
| 15° | 1562 | 438 |
| 25° | 1271 | 577 |
| 35° | 718 | 449 |
| 45° | 271 | 218 |
| 55° | 152 | 138 |
| 65° | 88 | 89 |
| 75° | 44 | 46 |
| 85° | 10 | 12 |
| 90° | 0 | |



TEST NUMBER: P207990

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBNMW1

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1820.0 |
| 2.5° | 1809.9 |
| 5° | 1786.2 |
| 7.5° | 1745.5 |
| 10° | 1691.3 |
| 12.5° | 1630.2 |
| 15° | 1562.5 |
| 17.5° | 1491.3 |
| 20° | 1416.7 |
| 22.5° | 1345.5 |
| 25° | 1271.0 |
| 27.5° | 1176.1 |
| 30° | 1047.3 |
| 32.5° | 894.8 |
| 35° | 718.5 |
| 37.5° | 555.8 |
| 40° | 430.4 |
| 42.5° | 335.5 |
| 45° | 271.1 |
| 47.5° | 220.3 |
| 50° | 193.2 |
| 52.5° | 172.9 |
| 55° | 152.5 |
| 57.5° | 135.6 |
| 60° | 118.6 |
| 62.5° | 101.7 |
| 65° | 88.1 |
| 67.5° | 78.0 |
| 70° | 64.4 |
| 72.5° | 54.2 |
| 75° | 44.1 |
| 77.5° | 33.9 |
| 80° | 23.7 |
| 82.5° | 16.9 |
| 85° | 10.2 |
| 87.5° | 3.4 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)