

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206473

Luminaire Tested: **LD4B50D010TE EU4B30509024 4LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206473
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509024 4LBCSMB1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3671.0 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206473

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P206473

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206473

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.6	4.0
10°-20°	417.7	11.4
20°-30°	627.9	17.1
30°-40°	745.0	20.3
40°-50°	737.3	20.1
50°-60°	579.1	15.8
60°-70°	324.7	8.8
70°-80°	91.2	2.5
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1192.2	32.5
0°-40°	1937.2	52.8
0°-60°	3253.6	88.6
0°-90°	3671.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3671.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1550	
5°	1548	147
15°	1482	418
25°	1363	628
35°	1195	745
45°	961	737
55°	653	579
65°	324	325
75°	79	91
85°	0	1
90°	0	



TEST NUMBER: P206473

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1550.1
2.5°	1544.8
5°	1547.5
7.5°	1534.3
10°	1518.5
12.5°	1500.1
15°	1481.7
17.5°	1458.0
20°	1426.4
22.5°	1394.8
25°	1363.2
27.5°	1329.0
30°	1284.3
32.5°	1239.5
35°	1194.8
37.5°	1142.2
40°	1081.6
42.5°	1023.7
45°	960.6
47.5°	889.5
50°	815.8
52.5°	731.6
55°	652.7
57.5°	563.2
60°	479.0
62.5°	402.7
65°	323.7
67.5°	255.3
70°	189.5
72.5°	129.0
75°	79.0
77.5°	39.5
80°	10.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)