

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205614

Luminaire Tested: **LD4B30D010 EU4B30508035 4LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205614  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30508035 4LBSWMH1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2977.7 lumens  
Efficiency: N/A  
Efficacy: 106.3 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205614

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205614

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90																			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79																			
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70																			
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62																			
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56																			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50																			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45																			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38																			
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205614

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBSWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.4	5.9
10°-20°	462.2	15.5
20°-30°	620.8	20.8
30°-40°	635.4	21.3
40°-50°	550.0	18.5
50°-60°	365.8	12.3
60°-70°	150.3	5.0
70°-80°	17.9	0.6
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1257.4	42.2
0°-40°	1892.9	63.6
0°-60°	2808.7	94.3
0°-90°	2977.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2977.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1887	
5°	1858	174
15°	1651	462
25°	1354	621
35°	1015	635
45°	716	550
55°	406	366
65°	148	150
75°	8	18
85°	0	1
90°	0	



TEST NUMBER: P205614

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1887.2
2.5°	1883.3
5°	1857.9
7.5°	1818.9
10°	1766.2
12.5°	1707.7
15°	1651.1
17.5°	1578.9
20°	1508.6
22.5°	1434.4
25°	1354.4
27.5°	1268.6
30°	1182.7
32.5°	1096.8
35°	1014.8
37.5°	936.8
40°	862.6
42.5°	788.5
45°	716.2
47.5°	640.1
50°	562.1
52.5°	484.0
55°	405.9
57.5°	337.6
60°	267.4
62.5°	203.0
65°	148.3
67.5°	97.6
70°	56.6
72.5°	27.3
75°	7.8
77.5°	3.9
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)