

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205620

Luminaire Tested: **LD4B30D010 EU4B30509035 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205620
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509035 4LBSWMH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2517.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205620

CATALOG NUMBER: LD4B30D010 EU4B30509035 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P205620

CATALOG NUMBER: LD4B30D010 EU4B30509035 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70		
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62		
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56		
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50		
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45		
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38		
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205620

CATALOG NUMBER: LD4B30D010 EU4B30509035 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	5.9
10°-20°	390.7	15.5
20°-30°	524.8	20.8
30°-40°	537.2	21.3
40°-50°	464.9	18.5
50°-60°	309.2	12.3
60°-70°	127.0	5.0
70°-80°	15.1	0.6
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1062.9	42.2
0°-40°	1600.1	63.6
0°-60°	2374.3	94.3
0°-90°	2517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2517.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1595	
5°	1571	147
15°	1396	391
25°	1145	525
35°	858	537
45°	606	465
55°	343	309
65°	125	127
75°	7	15
85°	0	1
90°	0	



TEST NUMBER: P205620

CATALOG NUMBER: LD4B30D010 EU4B30509035 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1595.3
2.5°	1592.0
5°	1570.6
7.5°	1537.6
10°	1493.0
12.5°	1443.5
15°	1395.7
17.5°	1334.6
20°	1275.3
22.5°	1212.6
25°	1144.9
27.5°	1072.3
30°	999.7
32.5°	927.2
35°	857.9
37.5°	791.9
40°	729.2
42.5°	666.5
45°	605.5
47.5°	541.1
50°	475.1
52.5°	409.1
55°	343.1
57.5°	285.4
60°	226.0
62.5°	171.6
65°	125.4
67.5°	82.5
70°	47.8
72.5°	23.1
75°	6.6
77.5°	3.3
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)