

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207401

Luminaire Tested: **LD4B50D010TE EU4B30509024 4LBMGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207401  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30509024 4LBMGPH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2028.4 lumens  
Efficiency: N/A  
Efficacy: 34.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207401

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBMGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207401

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBMGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86		
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68		
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207401

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBMGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	191.9	9.5
10°-20°	500.4	24.7
20°-30°	641.8	31.6
30°-40°	463.9	22.9
40°-50°	166.3	8.2
50°-60°	44.9	2.2
60°-70°	14.7	0.7
70°-80°	4.5	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1334.1	65.8
0°-40°	1798.0	88.6
0°-60°	2009.2	99.1
0°-90°	2028.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2028.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2085	
5°	2047	192
15°	1783	500
25°	1416	642
35°	742	464
45°	200	166
55°	47	45
65°	13	15
75°	4	5
85°	0	0
90°	0	



TEST NUMBER: P207401

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBMGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2085.3
2.5°	2076.8
5°	2047.0
7.5°	2000.1
10°	1936.1
12.5°	1863.6
15°	1782.6
17.5°	1701.5
20°	1620.5
22.5°	1526.7
25°	1415.8
27.5°	1287.9
30°	1125.8
32.5°	938.2
35°	742.0
37.5°	562.9
40°	409.4
42.5°	290.0
45°	200.4
47.5°	136.5
50°	89.6
52.5°	64.0
55°	46.9
57.5°	34.1
60°	25.6
62.5°	21.3
65°	12.8
67.5°	8.5
70°	8.5
72.5°	4.3
75°	4.3
77.5°	4.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)