

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206239

Luminaire Tested: **LD4B30D010 EU4B30508040 4LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206239  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30508040 4LBPSMW1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3222.9 lumens  
Efficiency: N/A  
Efficacy: 115.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206239

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P206239

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206239

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.0	3.8
10°-20°	350.7	10.9
20°-30°	528.2	16.4
30°-40°	628.5	19.5
40°-50°	627.4	19.5
50°-60°	510.2	15.8
60°-70°	313.9	9.7
70°-80°	121.6	3.8
80°-90°	19.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1001.9	31.1
0°-40°	1630.4	50.6
0°-60°	2768.0	85.9
0°-90°	3222.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3222.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1298	
5°	1295	123
15°	1245	351
25°	1150	528
35°	1006	628
45°	815	627
55°	571	510
65°	315	314
75°	111	122
85°	15	19
90°	0	



TEST NUMBER: P206239

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1298.5
2.5°	1300.4
5°	1294.7
7.5°	1287.1
10°	1277.5
12.5°	1260.3
15°	1245.0
17.5°	1222.1
20°	1197.3
22.5°	1174.4
25°	1149.6
27.5°	1115.2
30°	1080.8
32.5°	1048.4
35°	1006.4
37.5°	960.5
40°	918.5
42.5°	867.0
45°	815.4
47.5°	760.0
50°	700.8
52.5°	639.7
55°	571.0
57.5°	504.1
60°	439.2
62.5°	376.2
65°	315.1
67.5°	257.8
70°	204.3
72.5°	154.7
75°	110.8
77.5°	72.6
80°	43.9
82.5°	26.7
85°	15.3
87.5°	7.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)