

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208120

Luminaire Tested: **LD4B50D010TE EU4B30509024 4LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P208120  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30509024 4LBWL1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3720.2 lumens  
Efficiency: N/A  
Efficacy: 63.3 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P208120

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBWLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P208120

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBWLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P208120

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBWLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	222.9	6.0
10°-20°	703.5	18.9
20°-30°	1097.4	29.5
30°-40°	1067.8	28.7
40°-50°	533.3	14.3
50°-60°	82.5	2.2
60°-70°	10.0	0.3
70°-80°	2.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2023.8	54.4
0°-40°	3091.5	83.1
0°-60°	3707.4	99.7
0°-90°	3720.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3720.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2279	
5°	2309	223
15°	2484	703
25°	2412	1097
35°	1734	1068
45°	669	533
55°	68	83
65°	8	10
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P208120

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBWLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2279.4
2.5°	2287.9
5°	2309.2
7.5°	2343.3
10°	2385.9
12.5°	2441.3
15°	2483.9
17.5°	2518.0
20°	2522.3
22.5°	2492.4
25°	2411.5
27.5°	2292.2
30°	2143.1
32.5°	1955.6
35°	1734.1
37.5°	1491.2
40°	1235.6
42.5°	962.9
45°	668.9
47.5°	430.3
50°	259.9
52.5°	140.6
55°	68.2
57.5°	29.8
60°	17.0
62.5°	12.8
65°	8.5
67.5°	8.5
70°	4.3
72.5°	4.3
75°	4.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)