

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206755

Luminaire Tested: **LD4B30D010 EU4B30508040 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206755
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508040 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2622.8 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206755

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206755

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69		
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63		
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58		
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53		
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49		
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45		
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206755

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.9	6.1
10°-20°	491.5	18.7
20°-30°	756.1	28.8
30°-40°	729.5	27.8
40°-50°	380.4	14.5
50°-60°	80.1	3.1
60°-70°	18.6	0.7
70°-80°	7.2	0.3
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1406.6	53.6
0°-40°	2136.1	81.4
0°-60°	2596.5	99.0
0°-90°	2622.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2622.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1640	
5°	1654	159
15°	1739	492
25°	1657	756
35°	1184	730
45°	484	380
55°	72	80
65°	17	19
75°	7	7
85°	0	0
90°	0	



TEST NUMBER: P206755

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1639.9
2.5°	1643.3
5°	1653.6
7.5°	1667.4
10°	1687.9
12.5°	1715.4
15°	1739.4
17.5°	1753.1
20°	1742.8
22.5°	1722.3
25°	1657.1
27.5°	1578.2
30°	1475.2
32.5°	1338.0
35°	1183.6
37.5°	1015.5
40°	840.5
42.5°	665.6
45°	483.7
47.5°	325.9
50°	209.3
52.5°	126.9
55°	72.0
57.5°	44.6
60°	30.9
62.5°	24.0
65°	17.2
67.5°	13.7
70°	10.3
72.5°	10.3
75°	6.9
77.5°	3.4
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)