

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206245

Luminaire Tested: **LD4B30D010 EU4B30509040 4LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206245  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30509040 4LBPSMW1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2699.8 lumens  
Efficiency: N/A  
Efficacy: 96.4 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206245

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P206245

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206245

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.1	3.8
10°-20°	293.8	10.9
20°-30°	442.5	16.4
30°-40°	526.5	19.5
40°-50°	525.5	19.5
50°-60°	427.4	15.8
60°-70°	262.9	9.7
70°-80°	101.9	3.8
80°-90°	16.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	839.3	31.1
0°-40°	1365.8	50.6
0°-60°	2318.7	85.9
0°-90°	2699.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2699.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1088	
5°	1085	103
15°	1043	294
25°	963	442
35°	843	526
45°	683	526
55°	478	427
65°	264	263
75°	93	102
85°	13	16
90°	0	



TEST NUMBER: P206245

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1087.8
2.5°	1089.4
5°	1084.6
7.5°	1078.2
10°	1070.2
12.5°	1055.8
15°	1043.0
17.5°	1023.8
20°	1003.0
22.5°	983.8
25°	963.0
27.5°	934.2
30°	905.4
32.5°	878.2
35°	843.0
37.5°	804.6
40°	769.4
42.5°	726.2
45°	683.0
47.5°	636.7
50°	587.1
52.5°	535.9
55°	478.3
57.5°	422.3
60°	367.9
62.5°	315.1
65°	263.9
67.5°	216.0
70°	171.2
72.5°	129.6
75°	92.8
77.5°	60.8
80°	36.8
82.5°	22.4
85°	12.8
87.5°	6.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)