

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208115

Luminaire Tested: **LD4B50D010TE EU4B30508027 4LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208115
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508027 4LBWL1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4924.7 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208115
CATALOG NUMBER: LD4B50D010TE EU4B30508027 4LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208115

CATALOG NUMBER: LD4B50D010TE EU4B30508027 4LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70			
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49			
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45			
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208115

CATALOG NUMBER: LD4B50D010TE EU4B30508027 4LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.1	6.0
10°-20°	931.2	18.9
20°-30°	1452.7	29.5
30°-40°	1413.5	28.7
40°-50°	706.0	14.3
50°-60°	109.3	2.2
60°-70°	13.2	0.3
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2679.0	54.4
0°-40°	4092.5	83.1
0°-60°	4907.8	99.7
0°-90°	4924.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4924.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3018	
5°	3057	295
15°	3288	931
25°	3192	1453
35°	2296	1413
45°	886	706
55°	90	109
65°	11	13
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P208115

CATALOG NUMBER: LD4B50D010TE EU4B30508027 4LBWLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3017.5
2.5°	3028.7
5°	3056.9
7.5°	3102.1
10°	3158.5
12.5°	3231.8
15°	3288.2
17.5°	3333.3
20°	3339.0
22.5°	3299.5
25°	3192.3
27.5°	3034.4
30°	2837.0
32.5°	2588.8
35°	2295.5
37.5°	1974.0
40°	1635.6
42.5°	1274.7
45°	885.5
47.5°	569.7
50°	344.0
52.5°	186.1
55°	90.2
57.5°	39.5
60°	22.6
62.5°	16.9
65°	11.3
67.5°	11.3
70°	5.6
72.5°	5.6
75°	5.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)