

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205933

Luminaire Tested: **LD4B30D010 EU4B30509040 4LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509040 4LBSGPH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2281.7 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205933

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205933

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205933

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.8	4.4
10°-20°	280.1	12.3
20°-30°	408.5	17.9
30°-40°	465.8	20.4
40°-50°	446.8	19.6
50°-60°	342.2	15.0
60°-70°	187.8	8.2
70°-80°	49.9	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	788.3	34.6
0°-40°	1254.1	55.0
0°-60°	2043.2	89.5
0°-90°	2281.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2281.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1060	
5°	1052	100
15°	994	280
25°	887	408
35°	745	466
45°	580	447
55°	383	342
65°	189	188
75°	44	50
85°	0	1
90°	0	



TEST NUMBER: P205933

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1059.7
2.5°	1057.0
5°	1051.5
7.5°	1043.3
10°	1032.3
12.5°	1013.2
15°	994.0
17.5°	972.1
20°	947.4
22.5°	917.3
25°	887.2
27.5°	857.1
30°	818.7
32.5°	783.1
35°	744.8
37.5°	706.5
40°	668.1
42.5°	627.1
45°	580.5
47.5°	534.0
50°	484.7
52.5°	432.6
55°	383.4
57.5°	334.1
60°	282.0
62.5°	232.8
65°	188.9
67.5°	145.1
70°	106.8
72.5°	71.2
75°	43.8
77.5°	19.2
80°	5.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)