

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205829

Luminaire Tested: **LD4B30D010 EU4B30509040 4LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205829
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509040 4LBSWH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2500.6 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205829

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P205829

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205829

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.5	5.5
10°-20°	356.0	14.2
20°-30°	465.7	18.6
30°-40°	493.1	19.7
40°-50°	459.9	18.4
50°-60°	348.3	13.9
60°-70°	188.6	7.5
70°-80°	50.6	2.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.2	38.4
0°-40°	1452.3	58.1
0°-60°	2260.6	90.4
0°-90°	2500.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2500.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1491	
5°	1469	138
15°	1272	356
25°	1012	466
35°	788	493
45°	599	460
55°	391	348
65°	189	189
75°	44	51
85°	0	1
90°	0	



TEST NUMBER: P205829

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1491.3
2.5°	1485.8
5°	1469.4
7.5°	1433.8
10°	1387.3
12.5°	1332.6
15°	1272.4
17.5°	1204.0
20°	1143.8
22.5°	1075.4
25°	1012.4
27.5°	949.5
30°	889.3
32.5°	837.3
35°	788.1
37.5°	738.8
40°	692.3
42.5°	645.8
45°	599.3
47.5°	547.3
50°	495.3
52.5°	443.3
55°	391.3
57.5°	336.6
60°	284.6
62.5°	235.3
65°	188.8
67.5°	145.0
70°	106.7
72.5°	73.9
75°	43.8
77.5°	19.2
80°	5.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)