

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206887

Luminaire Tested: **LD4B50D010TE EU4B30509027 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509027 4LBWGPH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2794.9 lumens
Efficiency: N/A
Efficacy: 47.6 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206887

CATALOG NUMBER: LD4B50D010TE EU4B30509027 4LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P206887

CATALOG NUMBER: LD4B50D010TE EU4B30509027 4LBWGP1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92																			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76																			
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69																			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63																			
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57																			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53																			
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48																			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45																			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206887

CATALOG NUMBER: LD4B50D010TE EU4B30509027 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.7	6.8
10°-20°	537.8	19.2
20°-30°	771.2	27.6
30°-40°	726.1	26.0
40°-50°	401.0	14.3
50°-60°	128.6	4.6
60°-70°	32.2	1.2
70°-80°	7.6	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1498.7	53.6
0°-40°	2224.8	79.6
0°-60°	2754.4	98.6
0°-90°	2794.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2794.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2012	
5°	2002	190
15°	1905	538
25°	1692	771
35°	1178	726
45°	509	401
55°	131	129
65°	29	32
75°	5	8
85°	0	1
90°	0	



TEST NUMBER: P206887

CATALOG NUMBER: LD4B50D010TE EU4B30509027 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2011.6
2.5°	1997.1
5°	2001.9
7.5°	1987.4
10°	1963.1
12.5°	1938.9
15°	1905.0
17.5°	1875.9
20°	1827.4
22.5°	1759.6
25°	1691.7
27.5°	1599.6
30°	1478.4
32.5°	1342.7
35°	1177.9
37.5°	1003.4
40°	824.0
42.5°	659.2
45°	509.0
47.5°	382.9
50°	276.3
52.5°	193.9
55°	130.9
57.5°	87.3
60°	63.0
62.5°	43.6
65°	29.1
67.5°	19.4
70°	14.5
72.5°	9.7
75°	4.8
77.5°	4.8
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)