

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206784

Luminaire Tested: **LD4B50D010TE EU4B30509027 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509027 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3705.4 lumens
Efficiency: N/A
Efficacy: 63.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206784

CATALOG NUMBER: LD4B50D010TE EU4B30509027 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206784

CATALOG NUMBER: LD4B50D010TE EU4B30509027 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84			
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63			
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58			
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53			
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206784

CATALOG NUMBER: LD4B50D010TE EU4B30509027 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.5	6.1
10°-20°	694.5	18.7
20°-30°	1068.2	28.8
30°-40°	1030.7	27.8
40°-50°	537.4	14.5
50°-60°	113.1	3.1
60°-70°	26.3	0.7
70°-80°	10.2	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1987.2	53.6
0°-40°	3017.9	81.4
0°-60°	3668.4	99.0
0°-90°	3705.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3705.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2317	
5°	2336	224
15°	2457	694
25°	2341	1068
35°	1672	1031
45°	683	537
55°	102	113
65°	24	26
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P206784

CATALOG NUMBER: LD4B50D010TE EU4B30509027 4LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2316.9
2.5°	2321.7
5°	2336.3
7.5°	2355.7
10°	2384.7
12.5°	2423.5
15°	2457.4
17.5°	2476.8
20°	2462.3
22.5°	2433.2
25°	2341.1
27.5°	2229.6
30°	2084.2
32.5°	1890.3
35°	1672.2
37.5°	1434.7
40°	1187.5
42.5°	940.3
45°	683.4
47.5°	460.5
50°	295.7
52.5°	179.3
55°	101.8
57.5°	63.0
60°	43.6
62.5°	33.9
65°	24.2
67.5°	19.4
70°	14.5
72.5°	14.5
75°	9.7
77.5°	4.8
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)