

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208534

Luminaire Tested: **LD4B50D010TE EU4B30509727 4LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509727 4LBNWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2438.8 lumens
Efficiency: N/A
Efficacy: 41.5 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208534

CATALOG NUMBER: LD4B50D010TE EU4B30509727 4LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P208534

CATALOG NUMBER: LD4B50D010TE EU4B30509727 4LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95																			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89																			
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84																			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79																			
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75																			
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71																			
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67																			
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64																			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208534

CATALOG NUMBER: LD4B50D010TE EU4B30509727 4LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	423.8	17.4
10°-20°	795.1	32.6
20°-30°	713.4	29.3
30°-40°	409.3	16.8
40°-50°	81.7	3.3
50°-60°	10.3	0.4
60°-70°	4.7	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1932.3	79.2
0°-40°	2341.6	96.0
0°-60°	2433.6	99.8
0°-90°	2438.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2438.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5183	
5°	4766	424
15°	2855	795
25°	1541	713
35°	648	409
45°	88	82
55°	13	10
65°	4	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P208534

CATALOG NUMBER: LD4B50D010TE EU4B30509727 4LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5183.1
2.5°	5077.9
5°	4766.3
7.5°	4311.6
10°	3814.7
12.5°	3326.3
15°	2854.7
17.5°	2442.1
20°	2088.4
22.5°	1793.7
25°	1541.0
27.5°	1338.9
30°	1115.8
32.5°	888.4
35°	648.4
37.5°	442.1
40°	273.7
42.5°	164.2
45°	88.4
47.5°	37.9
50°	16.8
52.5°	12.6
55°	12.6
57.5°	8.4
60°	8.4
62.5°	4.2
65°	4.2
67.5°	4.2
70°	4.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)