

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252116

Luminaire Tested: **LD4B50D010TE EU4B30508030 4LBBA1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252116
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-4)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508030 4LBBA1MB
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE BLACK TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2599.1 lumens
Efficiency: N/A
Efficacy: 44.2 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.94
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252116

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBBA1MB

Luminous Intensity Polar Plot





TEST NUMBER: P252116

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBBA1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	253323
5°	252627
10°	250175
15°	246166
20°	238964
25°	220755
30°	179099
35°	111027
40°	52238
45°	18234
50°	5140
55°	3466
60°	2651
65°	2352
70°	1938
75°	1280
80°	1908
85°	0



TEST NUMBER: P252116

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBBA1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.7	9.4
10°-20°	685.8	26.4
20°-30°	921.8	35.5
30°-40°	588.9	22.7
40°-50°	125.2	4.8
50°-60°	18.9	0.7
60°-70°	9.2	0.4
70°-80°	4.0	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1852.3	71.3
0°-40°	2441.2	93.9
0°-60°	2585.3	99.5
0°-90°	2599.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2599.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2599	
5°	2582	245
15°	2440	686
25°	2053	922
35°	933	589
45°	132	125
55°	20	19
65°	10	9
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P252116

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBBA1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2599.3
2.5°	2595.9
5°	2582.3
7.5°	2558.6
10°	2528.0
12.5°	2487.3
15°	2439.8
17.5°	2378.7
20°	2304.1
22.5°	2198.9
25°	2052.9
27.5°	1849.4
30°	1591.5
32.5°	1272.5
35°	933.2
37.5°	637.9
40°	410.6
42.5°	244.3
45°	132.3
47.5°	67.9
50°	33.9
52.5°	23.8
55°	20.4
57.5°	17.0
60°	13.6
62.5°	10.2
65°	10.2
67.5°	6.8
70°	6.8
72.5°	3.4
75°	3.4
77.5°	3.4
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)