

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206358

Luminaire Tested: **LD4B40D010 EU4B30509024 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509024 4LBCSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3082.1 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206358

CATALOG NUMBER: LD4B40D010 EU4B30509024 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206358

CATALOG NUMBER: LD4B40D010 EU4B30509024 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206358

CATALOG NUMBER: LD4B40D010 EU4B30509024 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.3	3.9
10°-20°	339.5	11.0
20°-30°	510.8	16.6
30°-40°	605.3	19.6
40°-50°	602.4	19.5
50°-60°	485.6	15.8
60°-70°	293.8	9.5
70°-80°	109.1	3.5
80°-90°	16.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	969.6	31.5
0°-40°	1574.9	51.1
0°-60°	2662.9	86.4
0°-90°	3082.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3082.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1259	
5°	1253	119
15°	1203	340
25°	1109	511
35°	969	605
45°	784	602
55°	542	486
65°	295	294
75°	99	109
85°	13	16
90°	0	



TEST NUMBER: P206358

CATALOG NUMBER: LD4B40D010 EU4B30509024 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1258.8
2.5°	1258.8
5°	1253.2
7.5°	1249.4
10°	1238.2
12.5°	1219.6
15°	1202.8
17.5°	1184.1
20°	1161.7
22.5°	1139.3
25°	1109.4
27.5°	1077.6
30°	1042.1
32.5°	1008.5
35°	969.3
37.5°	928.2
40°	879.7
42.5°	833.0
45°	784.4
47.5°	730.2
50°	670.5
52.5°	608.8
55°	541.6
57.5°	481.9
60°	414.6
62.5°	354.9
65°	295.1
67.5°	239.1
70°	186.8
72.5°	140.1
75°	99.0
77.5°	63.5
80°	37.4
82.5°	22.4
85°	13.1
87.5°	5.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)