

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206353

Luminaire Tested: **LD4B40D010 EU4B30508027 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206353
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508027 4LBCSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4080.0 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206353

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206353

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206353

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	3.9
10°-20°	449.5	11.0
20°-30°	676.2	16.6
30°-40°	801.3	19.6
40°-50°	797.5	19.5
50°-60°	642.9	15.8
60°-70°	388.9	9.5
70°-80°	144.4	3.5
80°-90°	21.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1283.5	31.5
0°-40°	2084.9	51.1
0°-60°	3525.2	86.4
0°-90°	4080.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4080.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1666	
5°	1659	158
15°	1592	449
25°	1469	676
35°	1283	801
45°	1038	797
55°	717	643
65°	391	389
75°	131	144
85°	17	22
90°	0	



TEST NUMBER: P206353

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1666.4
2.5°	1666.4
5°	1659.0
7.5°	1654.0
10°	1639.2
12.5°	1614.5
15°	1592.2
17.5°	1567.5
20°	1537.8
22.5°	1508.1
25°	1468.6
27.5°	1426.6
30°	1379.6
32.5°	1335.1
35°	1283.2
37.5°	1228.8
40°	1164.5
42.5°	1102.7
45°	1038.4
47.5°	966.7
50°	887.6
52.5°	806.0
55°	717.0
57.5°	637.9
60°	548.9
62.5°	469.7
65°	390.6
67.5°	316.5
70°	247.2
72.5°	185.4
75°	131.0
77.5°	84.1
80°	49.4
82.5°	29.7
85°	17.3
87.5°	7.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)