

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207383

Luminaire Tested: **LD4B40D010 EU4B30508027 4LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508027 4LBMGPH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2111.0 lumens
Efficiency: N/A
Efficacy: 50.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207383

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P207383

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86																			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79																			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																			
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																			
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51																			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207383

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.7	9.5
10°-20°	520.8	24.7
20°-30°	668.0	31.6
30°-40°	482.8	22.9
40°-50°	173.1	8.2
50°-60°	46.7	2.2
60°-70°	15.3	0.7
70°-80°	4.6	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1388.4	65.8
0°-40°	1871.2	88.6
0°-60°	2091.0	99.1
0°-90°	2111.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2111.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2170	
5°	2130	200
15°	1855	521
25°	1474	668
35°	772	483
45°	209	173
55°	49	47
65°	13	15
75°	4	5
85°	0	0
90°	0	



TEST NUMBER: P207383

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2170.3
2.5°	2161.4
5°	2130.3
7.5°	2081.5
10°	2014.9
12.5°	1939.5
15°	1855.2
17.5°	1770.8
20°	1686.5
22.5°	1588.9
25°	1473.5
27.5°	1340.3
30°	1171.7
32.5°	976.4
35°	772.2
37.5°	585.8
40°	426.1
42.5°	301.8
45°	208.6
47.5°	142.0
50°	93.2
52.5°	66.6
55°	48.8
57.5°	35.5
60°	26.6
62.5°	22.2
65°	13.3
67.5°	8.9
70°	8.9
72.5°	4.4
75°	4.4
77.5°	4.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)