

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252127

Luminaire Tested: **LD4B50D010TE EU4B30509730 4LBBA1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252127
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-4)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509730 4LBBA1MB
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE BLACK TRIM
Light Source: (1) HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1940.0 lumens
Efficiency: N/A
Efficacy: 33.0 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.94
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252127

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBBA1MB

Luminous Intensity Polar Plot





TEST NUMBER: P252127

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBBA1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	189088
5°	188568
10°	186740
15°	183752
20°	178365
25°	164784
30°	133680
35°	82866
40°	38994
45°	13617
50°	3836
55°	2583
60°	1969
65°	1753
70°	1453
75°	941
80°	1403
85°	0



TEST NUMBER: P252127

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBBA1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.7	9.4
10°-20°	511.9	26.4
20°-30°	688.1	35.5
30°-40°	439.6	22.7
40°-50°	93.5	4.8
50°-60°	14.1	0.7
60°-70°	6.9	0.4
70°-80°	3.0	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1382.6	71.3
0°-40°	1822.2	93.9
0°-60°	1929.8	99.5
0°-90°	1940.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1940.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1940	
5°	1928	183
15°	1821	512
25°	1532	688
35°	696	440
45°	99	93
55°	15	14
65°	8	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P252127

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBBA1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1940.2
2.5°	1937.7
5°	1927.5
7.5°	1909.8
10°	1887.0
12.5°	1856.6
15°	1821.2
17.5°	1775.6
20°	1719.8
22.5°	1641.3
25°	1532.4
27.5°	1380.4
30°	1187.9
32.5°	949.8
35°	696.5
37.5°	476.2
40°	306.5
42.5°	182.4
45°	98.8
47.5°	50.7
50°	25.3
52.5°	17.7
55°	15.2
57.5°	12.7
60°	10.1
62.5°	7.6
65°	7.6
67.5°	5.1
70°	5.1
72.5°	2.5
75°	2.5
77.5°	2.5
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)