

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207589

Luminaire Tested: **LD4B40D010 EU4B30508027 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207589
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508027 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3060.1 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207589

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207589

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89				89
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80				80
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71				71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64				64
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58				58
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53				53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49				49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45				45
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42				42
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39				39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207589

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.3	7.0
10°-20°	577.2	18.9
20°-30°	767.5	25.1
30°-40°	627.8	20.5
40°-50°	365.6	11.9
50°-60°	242.5	7.9
60°-70°	159.5	5.2
70°-80°	84.1	2.7
80°-90°	20.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1560.1	51.0
0°-40°	2187.8	71.5
0°-60°	2796.0	91.4
0°-90°	3060.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3060.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2323	
5°	2296	215
15°	2057	577
25°	1685	768
35°	1002	628
45°	461	366
55°	270	243
65°	160	159
75°	80	84
85°	18	20
90°	0	



TEST NUMBER: P207589

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2323.0
2.5°	2318.6
5°	2296.4
7.5°	2243.2
10°	2185.6
12.5°	2132.4
15°	2057.0
17.5°	1972.8
20°	1901.8
22.5°	1804.3
25°	1684.6
27.5°	1556.0
30°	1392.0
32.5°	1197.0
35°	1001.9
37.5°	824.6
40°	669.4
42.5°	549.7
45°	461.1
47.5°	390.1
50°	341.4
52.5°	301.5
55°	270.4
57.5°	239.4
60°	208.4
62.5°	186.2
65°	159.6
67.5°	137.4
70°	115.3
72.5°	97.5
75°	79.8
77.5°	62.1
80°	44.3
82.5°	31.0
85°	17.7
87.5°	4.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)