

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252049

Luminaire Tested: **LD4B50D010TE EU4B30509730 4LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252049
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-3)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509730 4LBBA1MW
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4647.0 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.99
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252049

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252049

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	58	50	45	68	57	50	45	56	49	45	54	49	45	53	48	44	43			
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	39	61	50	43	38	49	43	38	48	42	38	47	42	38	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	316729
5°	313478
10°	304069
15°	291862
20°	278728
25°	260671
30°	226904
35°	175095
40°	129551
45°	101937
50°	87559
55°	79621
60°	72587
65°	67175
70°	62062
75°	58177
80°	54047
85°	50990



TEST NUMBER: P252049

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.6	6.5
10°-20°	813.0	17.5
20°-30°	1100.0	23.7
30°-40°	924.3	19.9
40°-50°	584.9	12.6
50°-60°	420.1	9.0
60°-70°	289.1	6.2
70°-80°	163.7	3.5
80°-90°	50.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2214.6	47.7
0°-40°	3138.9	67.5
0°-60°	4143.9	89.2
0°-90°	4647.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4647.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3250	
5°	3204	302
15°	2893	813
25°	2424	1100
35°	1472	924
45°	740	585
55°	469	420
65°	291	289
75°	154	164
85°	46	50
90°	0	



TEST NUMBER: P252049

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBBA1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3249.9
2.5°	3239.7
5°	3204.3
7.5°	3146.0
10°	3072.6
12.5°	2986.4
15°	2892.7
17.5°	2791.4
20°	2687.5
22.5°	2566.0
25°	2424.1
27.5°	2241.7
30°	2016.3
32.5°	1752.9
35°	1471.7
37.5°	1223.5
40°	1018.3
42.5°	858.7
45°	739.6
47.5°	648.5
50°	577.5
52.5°	519.3
55°	468.6
57.5°	417.9
60°	372.4
62.5°	329.3
65°	291.3
67.5°	253.3
70°	217.8
72.5°	184.9
75°	154.5
77.5°	124.1
80°	96.3
82.5°	70.9
85°	45.6
87.5°	20.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)