

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205625

Luminaire Tested: **LD4B40D010 EU4B30508027 4LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205625  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30508027 4LBSWMH1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3893.3 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205625

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205625

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70			
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62			
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38			
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205625

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBSWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	228.1	5.9
10°-20°	604.4	15.5
20°-30°	811.7	20.8
30°-40°	830.8	21.3
40°-50°	719.2	18.5
50°-60°	478.3	12.3
60°-70°	196.5	5.0
70°-80°	23.4	0.6
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1644.1	42.2
0°-40°	2474.9	63.6
0°-60°	3672.4	94.3
0°-90°	3893.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3893.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2468	
5°	2429	228
15°	2159	604
25°	1771	812
35°	1327	831
45°	936	719
55°	531	478
65°	194	196
75°	10	23
85°	0	1
90°	0	



TEST NUMBER: P205625

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2467.5
2.5°	2462.4
5°	2429.3
7.5°	2378.2
10°	2309.3
12.5°	2232.8
15°	2158.8
17.5°	2064.4
20°	1972.5
22.5°	1875.5
25°	1770.9
27.5°	1658.6
30°	1546.4
32.5°	1434.1
35°	1326.9
37.5°	1224.8
40°	1127.9
42.5°	1030.9
45°	936.5
47.5°	837.0
50°	734.9
52.5°	632.8
55°	530.8
57.5°	441.5
60°	349.6
62.5°	265.4
65°	193.9
67.5°	127.6
70°	74.0
72.5°	35.7
75°	10.2
77.5°	5.1
80°	2.6
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)