

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205754

Luminaire Tested: **LD4B50D010TE EU4B30509730 4LBSH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205754  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30509730 4LBSH1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3811.8 lumens  
Efficiency: N/A  
Efficacy: 64.9 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205754

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBSH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205754

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBSH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205754

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBSH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	186.7	4.9
10°-20°	507.5	13.3
20°-30°	704.8	18.5
30°-40°	769.2	20.2
40°-50°	717.5	18.8
50°-60°	544.6	14.3
60°-70°	298.2	7.8
70°-80°	82.0	2.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1399.1	36.7
0°-40°	2168.3	56.9
0°-60°	3430.4	90.0
0°-90°	3811.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3811.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1994	
5°	1977	187
15°	1809	508
25°	1532	705
35°	1230	769
45°	932	718
55°	609	545
65°	298	298
75°	71	82
85°	0	1
90°	0	



TEST NUMBER: P205754

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBSH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1993.5
2.5°	1993.5
5°	1976.8
7.5°	1951.6
10°	1913.8
12.5°	1863.4
15°	1808.9
17.5°	1741.7
20°	1678.8
22.5°	1603.2
25°	1531.9
27.5°	1460.5
30°	1380.8
32.5°	1305.3
35°	1229.7
37.5°	1154.2
40°	1082.8
42.5°	1007.3
45°	931.7
47.5°	856.2
50°	772.2
52.5°	692.5
55°	608.6
57.5°	528.8
60°	449.1
62.5°	369.3
65°	298.0
67.5°	230.8
70°	172.1
72.5°	117.5
75°	71.3
77.5°	33.6
80°	8.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)