

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206893

Luminaire Tested: **LD4B50D010TE EU4B30509730 4LBWGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206893  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30509730 4LBWGPH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2540.0 lumens  
Efficiency: N/A  
Efficacy: 43.2 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206893

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBWGP1

### Luminous Intensity Polar Plot





TEST NUMBER: P206893

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBWGP1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53			
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206893

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBWGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.4	6.8
10°-20°	488.7	19.2
20°-30°	700.9	27.6
30°-40°	659.9	26.0
40°-50°	364.5	14.3
50°-60°	116.9	4.6
60°-70°	29.2	1.2
70°-80°	6.9	0.3
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1362.0	53.6
0°-40°	2021.9	79.6
0°-60°	2503.3	98.6
0°-90°	2540.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2540.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1828	
5°	1819	172
15°	1731	489
25°	1538	701
35°	1070	660
45°	463	364
55°	119	117
65°	26	29
75°	4	7
85°	0	1
90°	0	



TEST NUMBER: P206893

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBWGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1828.2
2.5°	1815.0
5°	1819.4
7.5°	1806.2
10°	1784.2
12.5°	1762.1
15°	1731.3
17.5°	1704.9
20°	1660.8
22.5°	1599.1
25°	1537.5
27.5°	1453.8
30°	1343.6
32.5°	1220.3
35°	1070.5
37.5°	911.9
40°	748.9
42.5°	599.1
45°	462.6
47.5°	348.0
50°	251.1
52.5°	176.2
55°	118.9
57.5°	79.3
60°	57.3
62.5°	39.6
65°	26.4
67.5°	17.6
70°	13.2
72.5°	8.8
75°	4.4
77.5°	4.4
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)