

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208103

Luminaire Tested: **LD4B40D010 EU4B30508027 4LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508027 4LBWLI1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3871.6 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208103

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208103

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																			
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																			
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77																			
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70																			
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64																			
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58																			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54																			
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49																			
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45																			
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208103

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.0	6.0
10°-20°	732.1	18.9
20°-30°	1142.1	29.5
30°-40°	1111.3	28.7
40°-50°	555.0	14.3
50°-60°	85.9	2.2
60°-70°	10.4	0.3
70°-80°	2.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2106.2	54.4
0°-40°	3217.4	83.1
0°-60°	3858.4	99.7
0°-90°	3871.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3871.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2372	
5°	2403	232
15°	2585	732
25°	2510	1142
35°	1805	1111
45°	696	555
55°	71	86
65°	9	10
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P208103

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2372.2
2.5°	2381.1
5°	2403.3
7.5°	2438.8
10°	2483.1
12.5°	2540.7
15°	2585.1
17.5°	2620.6
20°	2625.0
22.5°	2594.0
25°	2509.7
27.5°	2385.5
30°	2230.4
32.5°	2035.3
35°	1804.7
37.5°	1551.9
40°	1285.9
42.5°	1002.1
45°	696.2
47.5°	447.8
50°	270.5
52.5°	146.3
55°	70.9
57.5°	31.0
60°	17.7
62.5°	13.3
65°	8.9
67.5°	8.9
70°	4.4
72.5°	4.4
75°	4.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)