

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208016

Luminaire Tested: **LD4B50D010TE EU4B30508035 4LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208016
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508035 4LBNMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3804.3 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208016

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P208016

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90																			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81																			
3	98	90	84	80	96	89	83	79	86	82	78	84	80	76	81	78	75	73																			
4	92	83	76	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61																			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56																			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	62	57	53	52																			
8	73	62	55	50	71	61	55	50	60	54	50	59	53	49	58	53	49	48																			
9	69	58	51	46	68	57	51	46	56	50	46	55	50	46	54	49	46	44																			
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208016

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.6	7.8
10°-20°	781.2	20.5
20°-30°	1028.2	27.0
30°-40°	800.4	21.0
40°-50°	388.7	10.2
50°-60°	245.6	6.5
60°-70°	158.4	4.2
70°-80°	82.8	2.2
80°-90°	20.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2107.9	55.4
0°-40°	2908.3	76.4
0°-60°	3542.6	93.1
0°-90°	3804.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3804.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3245	
5°	3185	299
15°	2786	781
25°	2266	1028
35°	1281	800
45°	484	389
55°	272	246
65°	157	158
75°	79	83
85°	18	21
90°	0	



TEST NUMBER: P208016

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3245.4
2.5°	3227.3
5°	3185.0
7.5°	3112.5
10°	3015.8
12.5°	2907.0
15°	2786.1
17.5°	2659.2
20°	2526.2
22.5°	2399.3
25°	2266.4
27.5°	2097.1
30°	1867.5
32.5°	1595.5
35°	1281.3
37.5°	991.2
40°	767.5
42.5°	598.3
45°	483.5
47.5°	392.8
50°	344.5
52.5°	308.2
55°	272.0
57.5°	241.7
60°	211.5
62.5°	181.3
65°	157.1
67.5°	139.0
70°	114.8
72.5°	96.7
75°	78.6
77.5°	60.4
80°	42.3
82.5°	30.2
85°	18.1
87.5°	6.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)